




Eaton N784-001-SC-MM

10/100 SC Multimode Fiber to Ethernet
Media Converter, 550M, 850nm

□□□□

PRODUCT NAME	Eaton Tripp Lite series media converter
CATALOG NUMBER	N784-001-SC-MM
UPC	037332183934
PRODUCT LENGTH/DEPTH	3.7 in
PRODUCT HEIGHT	1.02 in
PRODUCT WIDTH	2.76 in
PRODUCT WEIGHT	0.44 lb
COMPLIANCES	CE Marked RoHS FCC Compliant

□□□□	
TYPE	Fiber to Ethernet
ACCESSORIES	External Power Supply (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V/2A)
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
COLOR	Black
PACKAGE CONTENTS	User Manual External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz; 5V, 1.2A) 10/100 SC Multimode Media Converter, 550M, 850nm
SYSTEM REQUIREMENTS	10/100 Ethernet Network Multimode SC Fiber cable
CONNECTOR TYPE	Networking-copper Networking-fiber
PRODUCT FEATURES	Auto MDIX Support Wavelength Division Multiplexing (WDM)
NETWORK SPEED	100 Mbps (Fast Ethernet) 10 Mbps 10 Mbps; 100 Mbps
PRODUCT HIGHLIGHTS	Extends a 100Mb Ethernet signal up to 550M over Multimode Fiber Optic Cable Auto detects Full/Half Duplex Transfer Mode 2-year limited warranty (Worldwide) Supports Multimode 50/125 cable up to 2KM or 62.5/125 cable up to 550M
NETWORK SPEED DETAILS	10 Mbps; 100 Mbps
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	cUL FCC WEEE CE
SIDEA CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR1	SC DUPLEX (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 11 mm, positive pin, negative sleeve
TECHNOLOGY	Multimode Cat5/5e
FEATURES	Flex Center



OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 158°F (-20° to 70°C)
TRANSMISSION RANGE	550 m
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 1.2A
AC POWER ADAPTER OUTPUT SPECS (V / A)	5V / 2A
AC POWER ADAPTER CORD LENGTH	4.53 ft
CABLE COLOR	Black
ADAPTER	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A
HOUSING	Metal
LED INDICATORS	PWR (Power LED), L/A (Fiber port connection indicator), SD (Fiber signal indicator), SPD (Network speed), TP-L/A (Copper port connection indicator), FDX/COL (Full Duplex/Half Duplex)
DATA TRANSFER RATE	10 Mbps 100 Mbps
WAVELENGTH	850 nm
CONNECTOR GROUP	SC RJ45
CONNECTOR	SC duplex (female) RJ45 (female)
MODE	Multimode
NETWORK PORTS	RJ45 (FEMALE) SC (FEMALE)
OPTICAL PORT	SC
INPUT POWER SOURCE TYPE	AC Adapter
OPERATING MODE	Full/Half Duplex

