



## Eaton NITD32M40

Eaton Bussmann series low voltage british standard fuse, 32A, AC 415 V, V88/A1, 18 x 55 mm, gM, 32M40

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	NITD32M40
<b>UPC</b>	051712844383
<b>PRODUCT LENGTH/DEPTH</b>	57 mm
<b>PRODUCT HEIGHT</b>	18 mm
<b>PRODUCT WIDTH</b>	18 mm
<b>PRODUCT WEIGHT</b>	27.05 g
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	BS88 IEC 60269 EAC

□□□□

AMPERAGE RATING	32 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A1
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	42.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	32M40
RATED VOLTAGE AC	415 V
CLASS	Class gM
FUSE TYPE	NITD
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1.9 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/A1
CONSTRUCTION SIZE	A1
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	CM32FC Camaster fuse holder
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF  
CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250939en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

