

## Eaton NSD32M36

Eaton Bussmann series low voltage british standard fuse, 6 A, AC 415 V, V88/F2, 14 x 59 mm, gM

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	NSD32M36
<b>UPC</b>	051712844499
<b>PRODUCT LENGTH/DEPTH</b>	59 mm
<b>PRODUCT HEIGHT</b>	18 mm
<b>PRODUCT WIDTH</b>	18 mm
<b>PRODUCT WEIGHT</b>	16.2 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-2 BS88

<b>AMPERAGE RATING</b>	6 A
<b>FITTED WITH:</b>	Offset bladed tags
<b>CURRENT TYPE</b>	AC
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>MOTOR CURRENT RATING</b>	32M36
<b>RATED VOLTAGE AC</b>	415 V
<b>CLASS</b>	Class gM
<b>FUSE TYPE</b>	NSD
<b>UTILIZATION CATEGORY</b>	gM (motor protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	2.4 W
<b>CONNECTION</b>	Blade end
<b>CONSTRUCTION</b>	BS88/F2
<b>CONSTRUCTION SIZE</b>	F2
<b>FUSE SHAPE</b>	Offset bladed tags
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	32NNS Safeloc fuse holder
	SC32 Safeclip fuse holder
<b>VOLTAGE RATING</b>	415 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Fuse system E

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250942en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

