

Eaton NEXI150-3H-AT

Eaton NexiTech LED, Safety lighting / exit sign, 20m viewing distance, Escape route, Auto-Test, LED, Maintained / Non-Maintained operation, IP40, 150lm, 3 hour duration

PRODUCT NAME	Eaton NexiTech LED SC Emergency Luminaire
CATALOG NUMBER	NEXI150-3H-AT
PRODUCT LENGTH/DEPTH	290 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	110 mm
PRODUCT WEIGHT	0.254 kg
CERTIFICATIONS	CE

BATTERY VOLTAGE	3.6 VDC
BATTERY QUALITY	NiCd
PERMISSIBLE AMBIENT TEMPERATURE - MIN	5 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	30 °C
PROTECTION CLASS	II
DEGREE OF IMPACT RESISTANCE (IK)	IK 03
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DIAMETER	9999 in
DEGREE OF PROTECTION	IP40
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
LAMP HOLDER	None
LAMP POWER	1.5 W
TYPE OF INDICATOR	Not applicable
MONITORING EQUIPMENT	Automatic self test
POWER SUPPLY SYSTEM	Peripheral (individual battery)
CIRCUIT	Other
VOLTAGE TYPE	AC
NOMINAL CURRENT - MAX	14.1 mA
NOMINAL CURRENT - MIN	5.4 mA
POWER FACTOR	.55
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	3.1 W
RATED LIFE TIME L80/B10 AT 25 °C	70000 hour
TYPE OF CONTROL GEAR	LED operating device



	current-controlled
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC - MIN	220 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	30 °C
NOMINAL OPERATION TIME - MIN	3 hour
NOMINAL OPERATION TIME - MAX	3 hour
AUTONOMY	3 hours
MOUNTING METHOD	Surface mounting/recessed mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MATERIAL COVER	Plastic, transparent
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	False
BUILT-IN LENGTH	272 mm
BUILT-IN WIDTH	95 mm
BUILT-IN HEIGHT/DEPTH	96 mm
NUMBER OF POLES (NUMERIC)	2
IMPACT STRENGTH	IK03
KIND OF LUMINAIRE	Safety and exit sign luminaire
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	150 lm
LUMINOUS FLUX AT EMERGENCY OPERATION	150 lm
COLOR TEMPERATURE - MAX	5053 K
COLOR TEMPERATURE - MIN	5053 K
LIGHT DISTRIBUTOR	Reflector
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route lighting/signage
COLOR OF LIGHT	White

COLOR RENDERING INDEX (CRI)	70-79
EFFECTIVE LUMINOUS FLUX	60
LUMINOUS FLUX IN STANDBY MODE	60 lm
NUMBER OF LIGHTING HEADS	16
SUITABLE FOR NUMBER OF LAMPS	1
VIEWING DISTANCE	20 m
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	0.5 - 2.5mm ²
TESTING SYSTEM	Auto-Test

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

