

Eaton PDG13M0003MSAJ

Eaton Power Defense motor circuit protector, Globally Rated, Frame 1 Motor Circuit Protector, Three Pole, 3A, 65kA/480V, Adjustable Instantaneous Standard Calibrations, Standard Line and Load

PRODUCT NAME	Eaton Power Defense motor circuit protector
CATALOG NUMBER	PDG13M0003MSAJ
UPC	786679263433
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked CSA UL 489

AMPERAGE RATING	3 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD1 Global
TERMINALS	Standard Line and Load
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Three-pole
TYPE	Motor Protection
INTERRUPT RATING RANGE	35 kAIC Icu at 250 Vdc 100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC)
	25 kAIC at 600 V (UL/CSA) 70 kAIC Icu/50 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)
	100 kAIC at 240 V (UL) 35 kAIC Icu at 125 Vdc 65 kAIC at 480 V (UL)
VOLTAGE RATING - MAX	600 V

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.

