

Eaton NIT6

Eaton Bussmann series low voltage british standard fuse, 6A, AC 550 V, DC 250 V, V88/A1, 14 x 56 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	NIT6
UPC	051712392501
PRODUCT LENGTH/DEPTH	56 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	15.9 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 BS88

AMPERAGE RATING	6 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A1
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M4
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	44.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	NIT
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1.8 W
CONNECTION	44 mm fixing centre
CONSTRUCTION	BS88/A1
CONSTRUCTION SIZE	A1
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	CM32FC Camaster fuse holder RS20 Red spot fuse holder
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250978en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

