



Eaton NITD16

Eaton Bussmann series low voltage british standard fuse, 16A, AC 550 V, V88/A1, 14 x 55 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	NITD16
UPC	051712840101
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	15.55 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 BS88

□□□□

AMPERAGE RATING	16 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A1
CURRENT TYPE	AC
MOUNTING DIMENSION	M4
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	42.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
CLASS	Class gG/gL
FUSE TYPE	NITD
CONTACT MATERIAL	Offset bolted tag, HRC
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1.8 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/A1
CONSTRUCTION SIZE	A1
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC/DC AC
SUITABLE FOR	CM32FC Camaster fuse holder RS20 Red spot fuse holder
QUANTITY	20
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250978en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

