



Eaton PDU12IEC

Eaton Tripp Lite series basic PDU, 1PH, 1U,
C20 input, 1.9-3.8kW, 16A, 120-240V, 14
Outlets (12) C13 (2) C19

Specifications

PRODUCT NAME	Eaton Tripp Lite series basic PDU
CATALOG NUMBER	PDU12IEC
UPC	037332116253
PRODUCT LENGTH/DEPTH	4.25 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	19 in
PRODUCT WEIGHT	3.2 lb
WARRANTY	5 year limited
COMPLIANCES	RoHS CE Marked TAA Compliant
CERTIFICATIONS	RETIE UL 60950-1 NOM CSA Std. C22.2

FORM FACTOR	1U
PACKAGE CONTENTS	• PDU12IEC 1.9/3.8kW Single-Phase 120–240V Basic PDU • Mounting hardware • Owner's manual
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
MOUNTING DIRECTION	Horizontal
MATERIAL	Metal
INPUT CONNECTION	IEC-320 C20
CORD LENGTH	0
AMPERAGE RATING	16A
ELECTRIC CURRENT - MAX	16
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS C13	12
NUMBER OF OUTPUTS C19	2
FEATURES	Flex Center
OUTPUT RECEPTACLES	C13 C19
GROUNDING OPTIONS	Grounding lug
MINIMUM REQUIRED RACK DEPTH	7.8 in
OUTLET SPACING	Distance between Front (C13) outlets = 28.75mm; Distance between Rear (C19) outlets = 55mm; Distance between Rear (C13) outlets = 28.75mm
OVERLOAD PROTECTION	16A circuit breaker
RECOMMENDED ELECTRICAL SERVICE	Single-phase 16/20A 120-240V service
OUTPUT RECEPTACLES DETAILS	Compatible with Eaton Tripp Lite Power Cords
RECEPTACLES	• C13 • C19
INPUT CORD LENGTH	0 ft
SWITCH CONFIGURATION	No power switch

PRODUCT FEATURES	IEC-320 C20
CORD TYPE	C20 inlet accepts user supplied input cable with C19 output connection
AMPERAGE RATING DETAILS	Agency derated to 16A continuous (North America only)
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	120-240V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	1U rackmount, 0U vertical rackmount, wall-mount and undercounter installation supported
OUTPUT CAPACITY DETAILS	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V), 2.03kW (127V), 1.92kW (120V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
OUTPUT CAPACITY (KW)	3.8
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	5-year limited warranty (Worldwide) Switchless design prevents accidental shutdown 14 total outlets—8 rear C13, 2 rear C19 and 4 front C13 C20 inlet accepts wide variety of user-supplied power cords Compatible with Eaton Tripp Lite power cords to simplify deployment and enhance reliability Reversible all-metal housing Installs in rack, on wall or under counter
PDU PLUG TYPE	C20
PDU TYPE	Basic
PDU INPUT VOLTAGE	120 208
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	14
TAA COMPLIANCE	No

