



Eaton PDUMNH20

Eaton Tripp Lite Series Monitored PDU, 1PH, 1U, NEMA L5-20/5-20P input, 12 ft cord, LX interface, 1.9kW, 16A, 120V, 8 Outlets (8) 5-20R, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series metered input PDU
CATALOG NUMBER	PDUMNH20
UPC	037332152015
PRODUCT LENGTH/DEPTH	6.2 in
PRODUCT HEIGHT	1.7 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	6.5 lb
WARRANTY	2 year limited
COMPLIANCES	FCC Class A RoHS
CERTIFICATIONS	UL 60950-1 CSA certified NOM

FORM FACTOR	1U
PACKAGE CONTENTS	• Rack-mount PDU • Built-in LX Platform interface • L5-20R to 5-20P adapter • Plug retention plates • Rack-mounting brackets • Owner's manual
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
MOUNTING DIRECTION	Horizontal
MATERIAL	Metal
CORD LENGTH	12 ft
AMPERAGE RATING	16A
ELECTRIC CURRENT - MAX	16
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS 5-20R	8
FEATURES	Flex Center
SNMP	Yes
FRONT PANEL LCD DISPLAY	Digital meter reports PDU output current in amps
OUTPUT RECEPTACLES	5-15/20R
MINIMUM REQUIRED RACK DEPTH	11.2 in
NETWORK PORTS	RJ45 Network port, Micro-USB Configuration port, USB A port supports a variety of EnviroSense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules.
RECOMMENDED ELECTRICAL SERVICE	Single-phase 20A 120V service
RECEPTACLES	5-15/20R
INPUT CORD LENGTH	12 ft
TAA COMPLIANCE	Yes
PRODUCT FEATURES	TAA Compliant
COMMUNICATIONS	Micro-USB- to-USB A

CABLE	configuration/console Access cable
AMPERAGE RATING DETAILS	Agency de-rated to 16A continuous
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	120V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	1U horizontal rackmount in 2 or 4 post racks
OUTPUT CAPACITY DETAILS	1.92kW (120V) / 16A total capacity; 16A max per outlet
OUTPUT CAPACITY (KW)	1.92
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
NETWORK SPEED	100 Mbps (Fast Ethernet) 10 Mbps
PRODUCT HIGHLIGHTS	Temperature, humidity and contact-closure monitoring options Pre-installed WEBCARDLX with latest version of PADM20 for enhanced remote management 2-year limited warranty (Worldwide) 8 NEMA 5-15/20R outlets with included cord retention brackets Reports voltage, frequency and load level via ethernet interface NEMA L5-20P input with included 5-20P plug adapter Monitored 16A 120V PDU, 1U horizontal rackmount format Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
POWERALERT SOFTWARE	LX Platform Interface: PowerAlert Device Manager
SNMP COMPATIBILITY	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems

PDU PLUG TYPE	L5-20P 5-20P
PDU TYPE	Monitored
PDU INPUT VOLTAGE	120
HIGH AVAILABILITY PDU FEATURES	Remote network notifications
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	8



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

