



□□□□□

Eaton PVML-3-UNV1-EM1

Eaton Crouse-Hinds series Champ PVML LED light fixture with emergency back-up, Cool white, 0-10V dimming, No guard, Tempered glass lens, 3000 lumens, 125 lm/W, Copper-free aluminum, No mounting module, Type V, 100-277 Vac, 26W

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series Champ PVML LED light fixture with emergency back-up |
| CATALOG NUMBER | PVML-3-UNV1-EM1 |
| UPC | 662276968646 |
| PRODUCT LENGTH/DEPTH | 13.13 in |
| PRODUCT HEIGHT | 15.68 in |
| PRODUCT WIDTH | 12.75 in |
| PRODUCT WEIGHT | 32.7 lb |

| Certifications and compliances | |
|---------------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |
| INGRESS PROTECTION (IP) RATINGS | IP66 |

| Product specifications | |
|------------------------|---------------------------|
| LUMENS | 3000 |
| LUMENS PER WATT | 125 |
| COLOR TEMPERATURE | Cool white |
| MOUNTING METHOD | No mounting module |
| OPTICAL DISTRIBUTION | Type V |
| GUARD TYPE | No guard |
| VOLTAGE RATING | 100-277 Vac |
| MATERIAL | Cast copper-free aluminum |
| LENS MATERIAL | Tempered glass |
| SPECIAL FEATURES | Emergency driver system |
| DIMMING | 0-10 V |
| FREQUENCY RATING | 50/60 Hz |
| POWER FACTOR | > 0.90 |
| WATTAGE | 26 W |

| Links | |
|---------------------|--|
| 3D model | SP3D Design Package - Champ VMVL EM with Emergency Back-up Battery |
| Product literature | IF 1918 - Champ PVML Emergency LED Luminaires |
| | IF 1920 - Champ VMVL and PVML Emergency LED Battery and Driver Replacement Kit |
| Technical documents | Eaton Specification Sheet - PVML-3-UNV1-EM1 |
| Accessories | Champ PVML LED with Emergency Back-up Battery flyer |
| Related products | Crouse-Hinds series Champ PVML LED with Emergency Back-up catalog page |

