

## Eaton NITD4

Eaton Bussmann series low voltage british standard fuse, 4A, AC 550 V, V88/A1, 14 x 55 mm, gL/gG

|                         |   |
|-------------------------|---|
|                         |   |
| PRODUCT NAME            | Eaton Bussmann series<br>low voltage british<br>standard fuse |
| CATALOG NUMBER          | NITD4   |
| UPC                     | 051712840071  |
| PRODUCT<br>LENGTH/DEPTH | 55 mm   |
| PRODUCT HEIGHT          | 14 mm   |
| PRODUCT WIDTH           | 14 mm   |
| PRODUCT WEIGHT          | 14.65 g   |
| COMPLIANCES             | RoHS Compliant<br>CE Marked                                   |
| CERTIFICATIONS          | IEC 60269-2<br>BS88   |

|   |   |
|---|---|
|   |   |
| <b>AMPERAGE RATING</b>                                  | 4 A   |
| <b>FITTED WITH:</b>                                     | Offset bolted tags  |
| <b>FUSE SIZE</b>  | BS88/A1   |
| <b>CURRENT TYPE</b>                                     | AC  |
| <b>MOUNTING DIMENSION</b>                               | M4  |
| <b>CENTER-TO-CENTER<br/>DISTANCE OF<br/>CONNECTIONS</b> | 42.5 mm   |
| <b>BREAKING CAPACITY</b>                                | 80 kA   |
| <b>RATED SWITCHING<br/>CAPACITY</b>                     | 80 kA   |
| <b>RATED VOLTAGE AC</b>                                 | 550 V   |
| <b>CLASS</b>  | Class gG/gL   |
| <b>FUSE TYPE</b>  | NITD  |
| <b>UTILIZATION CATEGORY</b>                             | gL/gG (cable<br>protection/equipment<br>protection)         |
| <b>COLOR</b>  | None  |
| <b>INTERRUPT RATING</b>                                 | 80 kAIC   |
| <b>FUSE INDICATOR</b>                                   | None  |
| <b>INSULATED METAL<br/>GRIPPING LUGS (IMGL)</b>         | No  |
| <b>WATT LOSSES</b>                                      | 1.4 W   |
| <b>CONNECTION</b>                                       | Bolt-on   |
| <b>CONSTRUCTION</b>                                     | BS88/A1   |
| <b>CONSTRUCTION SIZE</b>                                | A1  |
| <b>FUSE SHAPE</b>                                       | Offset slotted bolted tags                                  |
| <b>VOLTAGE TYPE</b>                                     | AC  |
| <b>SUITABLE FOR</b>                                     | CM32FC Camaster fuse<br>holder<br>RS20 Red spot fuse holder |
| <b>VOLTAGE RATING</b>                                   | 550 V   |
| <b>TYPE</b>   | Fuse  |
| <b>APPLICATION</b>                                      | general industrial<br>applications                          |
| <b>FUSE SYSTEM<br/>(ACCORDING TO IEC<br/>60269)</b>     | Fuse system E   |

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250978en.pdf](#)

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

