



Eaton PXS24S16A002

Eaton Moeller series xEffect - PXS24
Electronic Protection Module. Electronic
overcurrent protection for 24V DC, fix 16A
with tripped signal out-, control in-put, w/o
supply terminals

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - PXS24 current monitoring relay
CATALOG NUMBER	PXS24S16A002
UPC	786689167592
PRODUCT LENGTH/DEPTH	127 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	0.118 kg
COMPLIANCES	CE UL508 RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

FEATURES

Green = OK; Red = Triggered
OFF = Channel not in operation
Two-colored

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF

Does not apply, since the

MCAD MODEL

[pxs24s.stp](#)

□□□□

[eaton-pxs24-success-story-cs011001en-en-us.pdf](#)

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Plug-in connection
SPECIAL FEATURES	<ul style="list-style-type: none"> • Inductive loads: up to 13 A • On/Off/Reset
TYPE	Automation engineering 24V
AMPERAGE RATING	16 A
VOLTAGE RATING	24 VDC (15 VDC - 30 VDC)
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	2.9 W
MOUNTING METHOD	Snap-fit on DIN rail (EN 60715)
DEGREE OF PROTECTION	IP20
VOLTAGE TYPE	DC
BUSBAR TYPE	LINE (+) and GND (-); max 60A in various lengths of up to 1m
NUMBER OF CHANNELS	1
TERMINAL TYPE	Push in terminals
TEXT FIELD TYPE	17.5 mm x 6 mm
ADJUSTABLE DELAY-ON ENERGIZATION TIME - MIN	0 s
ADJUSTABLE OFF-DELAY	0 s

TIME - MIN	
CURRENT MEASUREMENT - MAX	20.8 A
CURRENT MEASUREMENT - MIN	0 A
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
PERMITTED DELAY-ON ENERGIZATION TIME - MAX	0 s
PERMITTED OFF-DELAY TIME - MAX	0 s
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MAX	100 °C
PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MIN	-40 °C
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	30 V
FUNCTIONS	DC-voltage over current
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	15 V
RATED OPERATIONAL CURRENT (IE) FIX	16 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	16 A
TRIP TIME FOR ELECTRONIC TRIP	70 ms

AMBIENT OPERATING TEMPERATURE DETAILS	-30° C - 55° C
PROTECTION	Electronic
CAPACITIVE LOAD	Up to 20,000 µ F
OUTPUT TERMINALS	3x LOAD (+) and 3x GND (-)
OVERLOAD CURRENT AND SHORT-CIRCUIT CURRENT TRIP	Type 1.3 x IN with active current limitation
TERMINAL CAPACITY	2.5 mm² (flexible with ferrules) 4 mm² (rigid)
TYPE OF CURRENT	DC
VOLTAGE TYPE OF SUPPLY VOLTAGE	DC
VOLTAGE TYPE OF OPERATING VOLTAGE	DC
RATED SWITCH CURRENT	19 A
SUPPLY VOLTAGE AT DC - MIN	15 V
SUPPLY VOLTAGE AT DC - MAX	30 V
OPERATING VOLTAGE AT DC - MIN	15 V
OPERATING VOLTAGE AT DC - MAX	30 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

