



Eaton PDE26G0160TAAS

Eaton Moeller series Power Defense molded case circuit-breaker, 160 A, 36kA, 4p, screw terminal

□□□□

PRODUCT NAME	Eaton Moeller series Power Defense molded case circuit-breaker
CATALOG NUMBER	PDE26G0160TAAS
PRODUCT LENGTH/DEPTH	201 mm
PRODUCT HEIGHT	89 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	2.268 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC IEC/EN 60947

AMPERAGE RATING	160 A
VOLTAGE RATING	220 V - 440 V
CIRCUIT BREAKER FRAME TYPE	PDE2
FEATURES	Protection unit Motor drive optional
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

CHARACTERISTIC CURVE

[eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-006.jpg](#)

[eaton-circuit-breaker-power-defense-mccb-characteristic-curve-005.jpg](#)

[eaton-circuit-breaker-current-power-defense-mccb-characteristic-curve-021.jpg](#)

[eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-019.jpg](#)

[eaton-circuit-breaker-current-power-defense-mccb-characteristic-curve-008.jpg](#)

[eaton-power-defense-mccb-dimensions-004.jpg](#)

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Fixed Complete device in housing
UTILIZATION CATEGORY	A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
RATED CURRENT (IU)	160 A
MAX. RATED OPERATION VOLTAGE UE AC	440
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0

DEGREE OF PROTECTION	IP2X
DIRECTION OF INCOMING SUPPLY	Vertical and 90° in all directions
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Four-pole
FUNCTIONS	System and cable protection
TYPE	Circuit breaker
SPECIAL FEATURES	Thermally and magnetically adjustable (calibrated at 40 °C)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
POWER LOSS	58 W
RELEASE SYSTEM	Thermomagnetic release
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	1280 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	800 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	160 A
OVERLOAD CURRENT SETTING (IR) - MIN	128 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	36 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	22.5 kA

STANDARD TERMINALS	Screw terminal
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	4000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
VOLTAGE RATING (DC)	250 V
RATED INSULATION VOLTAGE (UI)	800 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
 Eaton House
 30 Pembroke Road
 Dublin 4, 0000
 Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

