



□□□□

# Eaton

## PDG32MH250P2MN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 250A High Override, 65kA/480V, PXR25 LSI w/ Modbus RTU and Relays, No Terminals

□□□□

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton Power Defense molded case circuit breaker |
| <b>CATALOG NUMBER</b>       | PDG32MH250P2MN                                  |
| <b>UPC</b>                  | 786679295632                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 109.1 mm  |
| <b>PRODUCT HEIGHT</b>       | 257.1 mm  |
| <b>PRODUCT WIDTH</b>        | 138.9 mm  |
| <b>PRODUCT WEIGHT</b>       | 5.2163 kg                                       |
| <b>COMPLIANCES</b>          | RoHS Compliant                                  |
| <b>CERTIFICATIONS</b>       | IEC 60947-2<br>UL 489<br>CCC Marked<br>CSA      |



Powering Business Worldwide



|   |   |
|---|---|
| <b>AMPERAGE RATING</b>                          | 250A High Override  |
| <b>VOLTAGE RATING</b>                           | 600 Vac   |
| <b>TRIP TYPE</b>                                | T291  |
| <b>CIRCUIT BREAKER TYPE</b>                     | PD3 Global  |
| <b>CIRCUIT BREAKER FRAME TYPE</b>               | Complete breaker  |
| <b>TERMINALS</b>                                | No Terminals  |
| <b>FRAME</b>                                    | 3   |
| <b>CLASS</b>                                    | Class A   |
| <b>COMMUNICATION</b>                            | Modbus RTU  |
| <b>INTERRUPT RATING</b>                         | 65 kAIC at 480 Vac  |
| <b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b> | 600   |
| <b>SWITCH OFF TECHNIQUE</b>                     | Electronic  |
| <b>VOLTAGE RATING - MAX</b>                     | 600 V   |
| <b>INTERRUPT RATING RANGE</b>                   | 100 kAIC @240V (UL)<br>15 kAIC Icu/ 7.5 kAIC Ics/<br>31.5 kAIC Icm @690V (IEC)<br>30 kAIC Icu/ 15 kAIC Ics/ 63<br>kAIC Icm @525V South<br>Africa (IEC)<br>70 kAIC Icu/ 53 kAIC Ics/<br>154 kAIC Icm @380-415V<br>(IEC)<br>50 kAIC Icu/ 30 kAIC Ics/<br>105 kAIC Icm @480V Brazil<br>(IEC)<br>50 kAIC Icu/ 40 kAIC Ics/<br>105 kAIC Icm @440V (IEC)<br>100 kAIC Icu/ 100 kAIC Ics/<br>220 kAIC Icm @240V (IEC)<br>22 kAIC Icu @250 Vdc<br>65 kAIC @480V (UL)<br>35 kAIC @600V (UL/CSA) |
| <b>NUMBER OF POLES</b>                          | Two-pole  |
| <b>SPECIAL FEATURES</b>                         | Modbus / relays   |



