



Eaton STD10

Eaton Bussmann series low voltage british standard fuse, 10A, AC 240 V, 12 x 47 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	STD10
UPC	051712588843
PRODUCT LENGTH/DEPTH	47 mm
PRODUCT HEIGHT	12 mm
PRODUCT WIDTH	13 mm
PRODUCT WEIGHT	10.9 g
COMPLIANCES	RoHS Compliant

□□□□

AMPERAGE RATING	10 A
FITTED WITH:	Offset bolted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	M4
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	35 mm
BREAKING CAPACITY	33 kA
RATED SWITCHING CAPACITY	33 kA
RATED VOLTAGE AC	240 V
CLASS	Class gG/gL
FUSE TYPE	STD
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	33 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1.2 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	240 V
TYPE	Fuse
APPLICATION	street lighting cut-outs
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk251015en.pdf](#)

