



□□□□□

Eaton TC100M160

Eaton Bussmann series low voltage british standard fuse, 160 A, AC 660 V, DC 350 V, V88/B1, 26 x 137 mm, gM, 100M160

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TC100M160
UPC	051712485098
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	34 mm
PRODUCT WIDTH	34 mm
PRODUCT WEIGHT	205.6 g
COMPLIANCES	Not Applicable
CERTIFICATIONS	IEC Rated

□□□□

USED WITH	RS200 fuse holder
AMPERAGE RATING	160 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B1
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	100M160
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CLASS	Class gM
FUSE TYPE	TC
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B1
CONSTRUCTION SIZE	B1
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
QUANTITY	10
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

