



□□□□□

Eaton TEF120-0262

Eaton TEF Return-Line Filter,
TEF120.25VG.16.S.P.-.G.5.-.E1.1,5.P.-., 25 VG,
Glass fiber fleece (VG), Nitrile, 145 psi (10
Bar), Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton TEF Return-Line Filter
CATALOG NUMBER	TEF120-0262
PRODUCT LENGTH/DEPTH	172.67 mm
PRODUCT HEIGHT	287.02 mm
PRODUCT WIDTH	108.01 mm
PRODUCT WEIGHT	1.5 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

0000	
CONNECTION TYPE	G 1" threaded
FILTER TYPE	Return filter
MATERIAL	Aluminium
APPLICATION	Mounted on top or in the reservoir with the outlet port returning to the reservoir
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	25 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	232 psi (16 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)
OPERATING PRESSURE - MAX	145 psi (10 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

