



## Eaton TF125

Eaton Bussmann series low voltage british standard fuse, 125A, AC 660 V, DC 350 V, V88/B2, 34 x 137 mm, gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	TF125
<b>UPC</b>	051712485180
<b>PRODUCT LENGTH/DEPTH</b>	137 mm
<b>PRODUCT HEIGHT</b>	34 mm
<b>PRODUCT WIDTH</b>	34 mm
<b>PRODUCT WEIGHT</b>	207.2 g
<b>CERTIFICATIONS</b>	Not Applicable

□□□□

<b>AMPERAGE RATING</b>	125 A
<b>FITTED WITH:</b>	Centre bolted tags
<b>FUSE SIZE</b>	BS88/B2
<b>CURRENT TYPE</b>	AC/DC
<b>MOUNTING DIMENSION</b>	M8
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	111 mm
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>RATED VOLTAGE AC</b>	660 V
<b>RATED VOLTAGE DC</b>	350 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	TF
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>CONNECTION</b>	111 mm fixing centre
<b>CONSTRUCTION</b>	BS88/B2
<b>CONSTRUCTION SIZE</b>	B2
<b>FUSE SHAPE</b>	Center bolted tags
<b>VOLTAGE TYPE</b>	AC/DC
<b>SUITABLE FOR</b>	RS200 Red spot fuse holder
<b>VOLTAGE RATING</b>	660 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Fuse system E

□□

DECLARATIONS OF  
CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

