

Eaton TF160

Eaton Bussmann series low voltage british standard fuse, 160A, AC 660 V, DC 350 V, V88/B2, 34 x 137 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TF160
UPC	051712392846
PRODUCT LENGTH/DEPTH	137 mm
PRODUCT HEIGHT	34 mm
PRODUCT WIDTH	34 mm
PRODUCT WEIGHT	200.8 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	160 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B2
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CLASS	Class gG/gL
FUSE TYPE	TF
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B2
CONSTRUCTION SIZE	B2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	RS200 Red spot fuse holder
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

