

Eaton TF200M250

Eaton Bussmann series low voltage british standard fuse, 200A, AC 660 V, DC 350 V, V88/B2, 34 x 137 mm, gM, 200M250

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TF200M250
UPC	051712485203
PRODUCT LENGTH/DEPTH	137 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	316.4 g
COMPLIANCES	Not Applicable
CERTIFICATIONS	BS

AMPERAGE RATING	250 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B2
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	200M250
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CLASS	Class gM
FUSE TYPE	TF
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B2
CONSTRUCTION SIZE	B2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	RS200 Red spot fuse holder
QUANTITY	10
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

