



□□□□□

Eaton TCP40A

Eaton Bussmann series low voltage british standard fuse, 40A, AC 660 V, DC 460 V, V88/A4, 23 x 109 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TCP40A
UPC	051712485159
PRODUCT LENGTH/DEPTH	109 mm
PRODUCT HEIGHT	23 mm
PRODUCT WIDTH	23 mm
PRODUCT WEIGHT	83.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated BS88 IEC 60269 EAC

□□□□

USED WITH	RS100H fuse holder
AMPERAGE RATING	40 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A4
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	93.7 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gG/gL
FUSE TYPE	TCP
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88/A4
CONSTRUCTION SIZE	A4
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	RS100 Red spot fuse holder
QUANTITY	10
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

