



□□□□□

Eaton TF200M315

Eaton Bussmann series low voltage british standard fuse, 200A, AC 550 V, V88/B2, 34 x 137 mm, gM, 200M315

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TF200M315
UPC	051712485210
PRODUCT LENGTH/DEPTH	137 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	306 g
COMPLIANCES	Not Applicable
CERTIFICATIONS	BS



Powering Business Worldwide

□□□□

AMPERAGE RATING	315 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	200M315
RATED VOLTAGE AC	550 V
CLASS	Class gM
FUSE TYPE	TF
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B2
CONSTRUCTION SIZE	B2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	RS200 Red spot fuse holder
QUANTITY	10
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

