



## Eaton TIS63M80

Eaton Bussmann series low voltage british standard fuse, 63A, AC 660 V, DC 460 V, V88/A3, 22 x 86 mm, gM, 63M80

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	TIS63M80
<b>UPC</b>	051712484978
<b>PRODUCT LENGTH/DEPTH</b>	58 mm
<b>PRODUCT HEIGHT</b>	26 mm
<b>PRODUCT WIDTH</b>	26 mm
<b>PRODUCT WEIGHT</b>	84.95 g
<b>COMPLIANCES</b>	Not Applicable
<b>CERTIFICATIONS</b>	IEC Rated



*Powering Business Worldwide*

□□□□

USED WITH	RS63H or MC63F fuse holder
AMPERAGE RATING	80 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A3
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	63M80
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gM
FUSE TYPE	TIS
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A3
CONSTRUCTION SIZE	A3
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	CM63F Camaster fuse holder RS63 Red spot fuse holder
QUANTITY	20
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

