

Eaton TMC3-150-2

Eaton Crouse-Hinds series TMC3 cable gland, 1.520" - 2.060" armor min./max., 1.630" - 2.310" cable range min./max., Armoured and non-armoured, Aluminum, 1.630" - 2.310" outer sheath min./max., Industrial protection, 1-1/2" NPT

PRODUCT NAME	Eaton Crouse-Hinds series TMC3 cable gland
CATALOG NUMBER	TMC3-150-2
UPC	662277129985
PRODUCT LENGTH/DEPTH	6.17 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	2.5 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IECEX/ATEX
NEC HAZARDOUS RATING	Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

PROTECTION TYPE	Industrial
GLAND TYPE	Armoured and non-armoured
CABLE TYPE	MC
	MC-HL
	TECK
	TC
	TC-ER
	TC-ER-HL
	ITC
	ITC-ER
	ITC-HL
	PLTC
	PLTC-ER
	ACIC
MATERIAL	Aluminum
THREAD SIZE	1-1/2"
THREAD TYPE	NPT
ARMOR (MIN/MAX)	1.520" - 2.060"
CABLE RANGE (MIN/MAX)	1.630" - 2.310"
OUTER SHEATH (MIN/MAX)	1.630" - 2.310"

[IF 1890 - TMC3 Cable Gland](#)

[Crouse-Hinds series TMC3 Armored Gland brochure](#)

[Crouse-Hinds series TMC3 Armored and Non-armored Cable Glands catalog page](#)

[TMC3 Armored Gland UL certification \(Class and Division\)](#)

[TMC3 Armored Gland ATEX/IECEx certification](#)

[TMC3 Armored Gland UL certification \(Zones\)](#)

[TMC3 Armored Gland Canadian certification \(Zones\)](#)

[TMC3 Armored Gland Canadian certification \(Class and Division\)](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

