

Eaton TIS63M100

Eaton Bussmann series low voltage british standard fuse, 63A, AC 660 V, DC 460 V, V88/A3, 22 x 86 mm, gM, 63M100

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TIS63M100
UPC	051712484961
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	26 mm
PRODUCT WIDTH	26 mm
PRODUCT WEIGHT	84.15 g
COMPLIANCES	Not Applicable
CERTIFICATIONS	IEC Rated

USED WITH	RS63H or MC63F fuse holder
AMPERAGE RATING	63 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A3
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	63M100
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gM
FUSE TYPE	TIS
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A3
CONSTRUCTION SIZE	A3
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	CM63F Camaster fuse holder RS63 Red spot fuse holder
QUANTITY	20
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

