

Eaton TKM315M355

Eaton Bussmann series low voltage british standard fuse, 355 A, AC 660 V, DC 460 V, 53 x 160 mm, gM

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TKM315M355
PRODUCT LENGTH/DEPTH	161 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	53 mm
PRODUCT WEIGHT	520 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

AMPERAGE RATING	355 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	133 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	315M355
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gM
FUSE TYPE	TKM
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	133 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250884en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

