



Eaton U360-004-R

4-Port USB 3.0 SuperSpeed Hub

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U360-004-R
UPC	037332161154
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.15 lb
WARRANTY	3 year limited
COMPLIANCES	CE Marked REACH FCC Compliant RoHS

TYPE	Hub
CHARGING PORTS DETAILS	Any of the 4 ports
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	Black
MATERIAL	ABS
USB HUB PORTS	Yes
CHARGING PORTS / AMPS	1.5A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	USB Charging
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
PACKAGE CONTENTS	External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A) USB 3.0 SuperSpeed 4-Port Hub User manual USB 3.0 Cable, 3-ft.
PRODUCT HIGHLIGHTS	USB 3.0 SuperSpeed Compatible 3-year limited warranty (Worldwide) 5Gbps Transfer Speed - 10X as fast as USB 2.0 External power supply included for use with more power hungry devices***NOTE***If your hub features white housing, see the FAQ tab on this page. All 4 ports are USB Battery Charging (BC) 1.2-compliant, providing up to 1.5A for charging mobile devices
PACKAGING TYPE	Box
PLUG COLOR	White Blue
EXTERNAL POWER SUPPLY CERTIFICATIONS	RoHS UL FCC cUL

POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
DC BARREL PLUG	OD: 3.5 x 1.35 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB 3.0 A (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	USB A (MALE)
CHARGING AMPS PER PORT	1.5 1.5 A
TECHNOLOGY	USB 3.x
FEATURES	Flex Center
CHARGING PORTS	USB-A: 5V 1.5A (7.5W)
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A
AC POWER ADAPTER CORD LENGTH	5 ft
NUMBER OF PORTS	4
NUMBER OF USB HUB PORTS	4
OUTPUT POWER CAPACITY	2 A
POWER CONSUMPTION	1 W
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
BTUS	2.4 BTU/Hr
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps)

