



Eaton TLM750

Eaton Bussmann series low voltage british standard fuse, 750A, AC 660 V, DC 350 V, V88/C3, 83 x 210 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TLM750
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	83 mm
PRODUCT WIDTH	83 mm
PRODUCT WEIGHT	0.015 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC



Powering Business Worldwide



AMPERAGE RATING	750 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/C3
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	183.8 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CLASS	Class gG/gL
FUSE TYPE	TLM
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	133/184 mm fixing centre
CONSTRUCTION	BS88/C3
CONSTRUCTION SIZE	C3
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E



DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250884en.pdf](#)

