



Eaton TLU800

Eaton Bussmann series low voltage british standard fuse, 800A, AC 660 V, DC 350 V, V88/D1, 84 x 200 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TLU800
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	84 mm
PRODUCT WIDTH	84 mm
PRODUCT WEIGHT	1905 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC



Powering Business Worldwide

□□□□

AMPERAGE RATING	800 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/D1
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M12
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	149 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CLASS	Class gG/gL
FUSE TYPE	TLU
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	149 mm fixing centre
CONSTRUCTION	BS88/D1
CONSTRUCTION SIZE	D1
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

