

Eaton TMC3-125-2

Eaton Crouse-Hinds series TMC3 cable gland, 1.280" - 1.610" armor min./max., 1.380" - 1.780" cable range min./max., Armoured and non-armoured, Aluminum, 1.380" - 1.780" outer sheath min./max., Industrial protection, 1-1/4" NPT

PRODUCT NAME	Eaton Crouse-Hinds series TMC3 cable gland
CATALOG NUMBER	TMC3-125-2
UPC	662277129961
PRODUCT LENGTH/DEPTH	6.01 in
PRODUCT HEIGHT	2.75 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	1.33 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IECEX/ATEX
NEC HAZARDOUS RATING	Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

PROTECTION TYPE	Industrial
GLAND TYPE	Armoured and non-armoured
CABLE TYPE	MC
	MC-HL
	TECK
	TC
	TC-ER
	TC-ER-HL
	ITC
	ITC-ER
	ITC-HL
	PLTC
	PLTC-ER
	ACIC
MATERIAL	Aluminum
THREAD SIZE	1-1/4"
THREAD TYPE	NPT
ARMOR (MIN/MAX)	1.280" - 1.610"
CABLE RANGE (MIN/MAX)	1.380" - 1.780"
OUTER SHEATH (MIN/MAX)	1.380" - 1.780"

[IF 1890 - TMC3 Cable Gland](#)

[Crouse-Hinds series TMC3 Armored Gland brochure](#)

[Crouse-Hinds series TMC3 Armored and Non-armored Cable Glands catalog page](#)

[TMC3 Armored Gland UL certification \(Zones\)](#)

[TMC3 Armored Gland UL certification \(Class and Division\)](#)

[TMC3 Armored Gland ATEX/IECEx certification](#)

[TMC3 Armored Gland Canadian certification \(Zones\)](#)

[TMC3 Armored Gland Canadian certification \(Class and Division\)](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

