



Eaton UT06GJC104PWH

Male plug with sealing glang backshell,
IP68/69K, 48 h salt spray, keying W;
UT06GJC104PWH

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06GJC104PWH
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III



Powering Business Worldwide

□□□□

□□

CURRENT RATING	13 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0 Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against acid bath Resistant against oil Resistant against gasoline Vibrations level 2g per NFF61030 Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Shock resistance 30g, 18ms per NFF61030 Resistant against basic bath
TEST CURRENT	13 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	500 V UL 500 V CSA 150 V IEC
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	4

PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
CABLE DIAMETER - MAX	8 mm
CABLE DIAMETER - MIN	1.5 mm
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	48 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

