



# Eaton

## UT07GJC104SWH01

Female jam nut receptacle with sealing  
glang backshell, IP67, 96 h salt spray, keying  
W; UT07GJC104SWH01

□□□□

|                       |                                                                           |
|-----------------------|---------------------------------------------------------------------------|
| <b>PRODUCT NAME</b>   | Eaton Souriau UTO series<br>metal IP68/69k connector<br>for intensive use |
| <b>CATALOG NUMBER</b> | UT07GJC104SWH01                                                           |
| <b>COMPLIANCES</b>    | UL 1977<br>Overvoltage category III /<br>pollution degree III             |



Powering Business Worldwide

□□□□

□□

|                                   |                                                                                                                                                                                                                                                                                                                                              |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CURRENT RATING</b>             | 10 A UL<br>13 A IEC                                                                                                                                                                                                                                                                                                                          |
| <b>FITTED WITH:</b>               | Last mate first break capability(optional)<br>First mate last break capability(optional)                                                                                                                                                                                                                                                     |
| <b>ENVIRONMENTAL CONDITIONS</b>   | Fire and smoke rating HL2<br>R22 and HL2 R23 following EN 45 545<br>Fire & Smoke<br>Flammability rating UL94 V0<br>RoHS<br>REACH                                                                                                                                                                                                             |
| <b>ENVIRONMENTAL RESISTANCE</b>   | Resistant against mineral oil<br>Vibrations level 2g per NFF61030<br>Resistant against acid bath<br><br>Resistant against oil<br>Resistant against basic bath<br>Shock resistance 30g, 18ms per NFF61030<br>Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I<br>Resistant against gasoline<br>Shock resistance 50g, 11ms per MIL-C-26482 I |
| <b>TEST CURRENT</b>               | 10 A UL<br>7 A CSA<br>13 A IEC                                                                                                                                                                                                                                                                                                               |
| <b>TEST VOLTAGE</b>               | 500 V UL<br>150 V IEC<br>500 V CSA                                                                                                                                                                                                                                                                                                           |
| <b>BACKSHELL ANGLE</b>            | Straight                                                                                                                                                                                                                                                                                                                                     |
| <b>BACKSHELL TYPE</b>             | Sealing Gland                                                                                                                                                                                                                                                                                                                                |
| <b>CONNECTOR ACCESSORY OPTION</b> | Delivered with connector                                                                                                                                                                                                                                                                                                                     |
| <b>CONNECTOR ORIENTATION</b>      | W                                                                                                                                                                                                                                                                                                                                            |
| <b>CONNECTOR TYPE</b>             | Receptacle                                                                                                                                                                                                                                                                                                                                   |
| <b>CONTACT DELIVERY</b>           | Not delivered                                                                                                                                                                                                                                                                                                                                |
| <b>CONTACT GENDER</b>             | Socket (Female)                                                                                                                                                                                                                                                                                                                              |
| <b>CONTACT TYPE</b>               | Crimp                                                                                                                                                                                                                                                                                                                                        |
| <b>COUPLING TYPE</b>              | 1/3 Bayonet                                                                                                                                                                                                                                                                                                                                  |
| <b>DEGREE OF PROTECTION</b>       | IP67                                                                                                                                                                                                                                                                                                                                         |
| <b>INSERT MATERIAL</b>            | Polyamide                                                                                                                                                                                                                                                                                                                                    |
| <b>LAYOUT</b>                     | 4                                                                                                                                                                                                                                                                                                                                            |

|                             |                    |
|-----------------------------|--------------------|
| PLATING                     | Nickel             |
| SHELL MATERIAL              | Zinc alloy         |
| SHELL SIZE                  | 10                 |
| CABLE DIAMETER - MAX        | 8 mm               |
| CABLE DIAMETER - MIN        | 1.5 mm             |
| MATING CYCLES               | 500                |
| OPERATING TEMPERATURE - MAX | 105 °C             |
| OPERATING TEMPERATURE - MIN | -40 °C             |
| RECEPTACLE TYPE             | Jam Nut Receptacle |
| NUMBER OF CONTACTS          | 4                  |
| NUMBER OF CAVITY #16        | 4                  |
| NUT MATERIAL                | Aluminium          |
| SALT SPRAY                  | 96 hour            |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



0000  
Eaton House  
30 Pembroke Road  
Dublin 4, 0000  
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

