



Eaton UT07GJC147PH

Male jam nut receptacle with sealing gland
backshell, IP67, 48 h salt spray;
UT07GJC147PH

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GJC147PH
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	10 A UL 16 A IEC
FITTED WITH:	First mate last break capability Layout with ground cavity
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH Fire & Smoke Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 RoHS
ENVIRONMENTAL RESISTANCE	Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 2g per NFF61030 Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against gasoline Resistant against mineral oil Shock resistance 30g, 18ms per NFF61030 Resistant against basic bath Resistant against acid bath Resistant against oil
TEST CURRENT	10 A UL 7 A CSA 16 A IEC
TEST VOLTAGE	500 V UL 150 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Polyamide
LAYOUT	7
PLATING	Nickel

SHELL MATERIAL	Zinc alloy
SHELL SIZE	14
CABLE DIAMETER - MAX	14 mm
CABLE DIAMETER - MIN	5 mm
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #16	7
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

