

Eaton UT07GN104PWH6

Male jam nut receptacle with single wire backshell, IP68/69K, 48 h salt spray, keying W; UT07GN104PWH6

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN104PWH6
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	10 A UL 13 A IEC
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire & Smoke Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 RoHS Flammability rating UL94 V0 REACH
ENVIRONMENTAL RESISTANCE	Vibrations level 2g per NFF61030 Resistant against oil Resistant against mineral oil Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against acid bath Shock resistance 30g, 18ms per NFF61030 Resistant against gasoline Resistant against basic bath Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I
TEST CURRENT	13 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	500 V UL 150 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
LAYOUT	4
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

