

Eaton

UT07GN104PWH601

Male jam nut receptacle with single wire backshell, IP68/69K, 96 h salt spray, keying W; UT07GN104PWH601

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN104PWH601
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	13 A IEC 10 A UL
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 V0 Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke REACH
ENVIRONMENTAL RESISTANCE	Resistant against basic bath Resistant against mineral oil Vibrations level 2g per NFF61030 Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Shock resistance 30g, 18ms per NFF61030 Resistant against acid bath Resistant against gasoline Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against oil
TEST CURRENT	10 A UL 13 A IEC 7 A CSA
TEST VOLTAGE	500 V CSA 150 V IEC 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
LAYOUT	4
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: