

Eaton UT07GN128SH601

Female jam nut receptacle with single wire backshell, IP68/69K, 96 h salt spray;
UT07GN128SH601

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN128SH601
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 RoHS Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 REACH Fire & Smoke
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against oil Vibrations level 2g per NFF61030 Shock resistance 30g, 18ms per NFF61030 Resistant against basic bath Resistant against mineral oil Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against acid bath
TEST CURRENT	10 A IEC 7 A CSA 10 A UL
TEST VOLTAGE	500 V UL 125 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide



LAYOUT	8
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

