



Eaton UT07GN128SWH6

Female jam nut receptacle with single wire backshell, IP68/69K, 48 h salt spray, keying W; UT07GN128SWH6

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN128SWH6
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III



Powering Business Worldwide

□□□□

□□

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire & Smoke Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Flammability rating UL94 V0 RoHS REACH
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil Resistant against basic bath Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 2g per NFF61030 Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against acid bath
TEST CURRENT	7 A CSA 10 A UL 10 A IEC
TEST VOLTAGE	125 V IEC 500 V CSA 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	8
PLATING	Nickel

SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

