


Eaton UT0W7106SH

Female jam nut receptacle IP67, 48 h salt spray; UT0W7106SH

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT0W7106SH
PRODUCT LENGTH/DEPTH	33.9 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	25.4 g
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	5 A UL 7 A IEC
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	Fire & Smoke REACH RoHS Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against oil Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against gasoline Resistant against basic bath Resistant against acid bath Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I
TEST CURRENT	5 A UL 4 A CSA 7 A IEC
TEST VOLTAGE	250 V CSA 250 V UL 80 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Polyamide
LAYOUT	6
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

