



□□□□□

Eaton UTG0148PH

Male square flange receptacle, IP65;
UTG0148PH

□□□□

PRODUCT NAME	Eaton Souriau UTG series metal and plastic connector for heavy use
CATALOG NUMBER	UTG0148PH
PRODUCT LENGTH/DEPTH	31.7 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	11 g

FITTED WITH:	Last mate first break capability Layout with ground cavity First mate last break capability
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP65
INSERT MATERIAL	Polyamide
LAYOUT	8
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #12	4
NUMBER OF CAVITY #16	4
SALT SPRAY	48 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: