

Eaton UTG01619P

Male square flange receptacle; UTG01619P

PRODUCT NAME	Eaton Souriau UTG series metal and plastic connector for heavy use
CATALOG NUMBER	UTG01619P
PRODUCT LENGTH/DEPTH	31.7 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	13.3 g

FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
---------------------	--

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 RoHS REACH
-------------------------------------	---

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
---------------------------------------	--

CONNECTOR TYPE	Receptacle
-----------------------	------------

CONTACT DELIVERY	Not delivered
-------------------------	---------------

CONTACT GENDER	Pin (Male)
-----------------------	------------

CONTACT TYPE	Crimp
---------------------	-------

COUPLING TYPE	1/3 Bayonet
----------------------	-------------

DEGREE OF PROTECTION	IP40
-----------------------------	------

INSERT MATERIAL	Polyamide
------------------------	-----------

LAYOUT	19
---------------	----

SHELL MATERIAL	Metal & Plastic
-----------------------	-----------------

SHELL SIZE	16
-------------------	----

MATING CYCLES	500
----------------------	-----

OPERATING TEMPERATURE - MAX	105 °C
--	--------

OPERATING TEMPERATURE - MIN	-40 °C
--	--------

RECEPTACLE TYPE	Square Flange Receptacle
------------------------	--------------------------

NUMBER OF CONTACTS	19
---------------------------	----

NUMBER OF CAVITY #16	19
-----------------------------	----

SALT SPRAY	48 hour
-------------------	---------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
