

Eaton UT07GN147SH01

Female jam nut receptacle with single wire backshell, IP67, 96 h salt spray;
UT07GN147SH01

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN147SH01
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	10 A UL 16 A IEC
FITTED WITH:	First mate last break capability Layout with ground cavity
ENVIRONMENTAL CONDITIONS	REACH Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke Flammability rating UL94 V0 RoHS
ENVIRONMENTAL RESISTANCE	Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 2g per NFF61030 Resistant against gasoline Resistant against basic bath Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil Resistant against acid bath Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against oil
TEST CURRENT	10 A UL 16 A IEC 7 A CSA
TEST VOLTAGE	500 V CSA 150 V IEC 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Polyamide



LAYOUT	7
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #16	7
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

