

Eaton UTG01619SH

Female square flange receptacle, IP65;
UTG01619SH

PRODUCT NAME	Eaton Souriau UTG series metal and plastic connector for heavy use
CATALOG NUMBER	UTG01619SH
PRODUCT LENGTH/DEPTH	24.3 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	13.3 g



FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP65
INSERT MATERIAL	Polyamide
LAYOUT	19
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	16
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #16	19
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

