

Eaton UTG0247PB

Male square flange receptacle, packed by 100 pcs; UTG0247PB

PRODUCT NAME	Eaton Souriau UTG series metal and plastic connector for heavy use
CATALOG NUMBER	UTG0247PB
PRODUCT LENGTH/DEPTH	33.3 mm
PRODUCT HEIGHT	42.9 mm
PRODUCT WIDTH	42.9 mm
PRODUCT WEIGHT	35 g



FITTED WITH:	Last mate first break capability Layout with ground cavity First mate last break capability
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP40
INSERT MATERIAL	Polyamide
LAYOUT	7
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	24
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	9
NUMBER OF CAVITY #16	2
NUMBER OF CAVITY #8 POWER	7
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

