

Eaton

UTL6122G1W5P14AWG

Evaluation kit, with male plug and contacts,
2G1W5 layout; UTL6122G1W5P14AWG

PRODUCT NAME	Eaton Souriau UTL series uL/IEC power and control supply
CATALOG NUMBER	UTL6122G1W5P14AWG
PRODUCT LENGTH/DEPTH	39.4 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	28 mm
PRODUCT WEIGHT	12 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	16 A IEC 16 A UL
FITTED WITH:	First mate last break capability Layout with ground cavity
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against acid bath Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against gasoline
TEST CURRENT	16 A UL16 A IEC
TEST VOLTAGE	600 V UL 500 V IEC
CONNECTOR ACCESSORY OPTION	Only to be overmolded
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	2G1W5
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	1000
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	3
NUMBER OF CAVITY #20	5



SALT SPRAY

1000 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

