

## Eaton UTS012E4P

Plastic square flange receptacle, without backshell, with 4 male solder contacts, IP68/69K in unmated conditions; UTS012E4P

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS012E4P
<b>PRODUCT LENGTH/DEPTH</b>	21.5 mm
<b>PRODUCT HEIGHT</b>	26.2 mm
<b>PRODUCT WIDTH</b>	26.2 mm
<b>PRODUCT WEIGHT</b>	9.3 g
<b>COMPLIANCES</b>	ROHS exemption 6.c UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	16 A IEC 10 A UL
FITTED WITH:	First mate last break capability Last mate first break capability(optional) Layout with ground cavity
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB RoHS REACH
ENVIRONMENTAL RESISTANCE	Resistant against acid bath  Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against gasoline
TEST CURRENT	7 A CSA 10 A UL 16 A IEC
TEST VOLTAGE	500 V UL 300 V IEC 500 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	4
SHELL MATERIAL	Plastic
SHELL SIZE	12



MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

