

# Eaton

## UTL7102G1W3P14AWG

Evaluation kit, with male jam nut receptacle and contacts, 2G1W3 layout;  
UTL7102G1W3P14AWG

<b>PRODUCT NAME</b>	Eaton Souriau UTL series uL/IEC power and control supply
<b>CATALOG NUMBER</b>	UTL7102G1W3P14AWG
<b>PRODUCT LENGTH/DEPTH</b>	28.6 mm
<b>PRODUCT HEIGHT</b>	28.6 mm
<b>PRODUCT WIDTH</b>	28.6 mm
<b>PRODUCT WEIGHT</b>	17 g
<b>COMPLIANCES</b>	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	16 A UL 16 A IEC
FITTED WITH:	First mate last break capability Layout with ground cavity
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against basic bath Resistant against acid bath  UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against mineral oil
TEST CURRENT	16 A UL16 A IEC
TEST VOLTAGE	500 V IEC 600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	2G1W3
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	1000
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #16	3
NUMBER OF CAVITY #20	3



NUT MATERIAL	Plastic
SALT SPRAY	1000 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

