

Eaton UTS014D19SW

Plastic square flange receptacle, without backshell, with 19 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS014D19SW

| | |
|-----------------------------|---|
| | |
| PRODUCT NAME | Eaton Souriau UTS series plastic waterproof IP68/69k connector |
| CATALOG NUMBER | UTS014D19SW |
| PRODUCT LENGTH/DEPTH | 21.5 mm |
| PRODUCT HEIGHT | 28.6 mm |
| PRODUCT WIDTH | 28.6 mm |
| PRODUCT WEIGHT | 18.1 g |
| COMPLIANCES | CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) |

| | |
|-----------------------------|---|
| | |
| CURRENT RATING | 5 A IEC 5 A UL |
| ENVIRONMENTAL CONDITIONS | Flammability rating UL94 HB REACH RoHS |
| ENVIRONMENTAL RESISTANCE | Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against oil |
| TEST CURRENT | 5 A IEC 4 A CSA 5 A UL |
| TEST VOLTAGE | 32 V IEC 250 V UL 250 V CSA |
| CONNECTOR ACCESSORY OPTION | No backshell possibility |
| CONNECTOR ORIENTATION | W |
| CONNECTOR TYPE | Receptacle |
| CONTACT DELIVERY | Loaded |
| CONTACT GENDER | Socket (Female) |
| CONTACT PLATING | Gold |
| CONTACT TYPE | PCB |
| COUPLING TYPE | 1/3 Bayonet |
| DEGREE OF PROTECTION | IP68 |
| INSERT MATERIAL | Neoprene |
| LAYOUT | 19 |
| SHELL MATERIAL | Plastic |
| SHELL SIZE | 14 |
| MATING CYCLES | 250 |
| OPERATING TEMPERATURE - MAX | 105 °C |
| OPERATING TEMPERATURE - MIN | -40 °C |



| | |
|----------------------|--------------------------|
| RECEPTACLE TYPE | Square Flange Receptacle |
| NUMBER OF CONTACTS | 19 |
| NUMBER OF CAVITY #20 | 19 |
| SALT SPRAY | 500 hour |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

