

# Eaton UTS714D15PW

Plastic jam nut receptacle, without backshell, with 15 male PCB contacts, IP68/69K in unmated conditions, keying W; UTS714D15PW

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS714D15PW
<b>PRODUCT LENGTH/DEPTH</b>	25.3 mm
<b>PRODUCT HEIGHT</b>	34.9 mm
<b>PRODUCT WIDTH</b>	34.9 mm
<b>PRODUCT WEIGHT</b>	24.8 g
<b>COMPLIANCES</b>	ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)



Powering Business Worldwide

<b>CURRENT RATING</b>	4 A IEC 12 A UL
<b>ENVIRONMENTAL CONDITIONS</b>	REACH RoHS Flammability rating UL94 HB
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against basic bath Resistant against acid bath  UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline
<b>TEST CURRENT</b>	12 A UL 4 A IEC 12 A CSA
<b>TEST VOLTAGE</b>	600 V UL 600 V CSA 50 V IEC
<b>CONNECTOR ACCESSORY OPTION</b>	No backshell possibility
<b>CONNECTOR ORIENTATION</b>	W
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Loaded
<b>CONTACT GENDER</b>	Pin (Male)
<b>CONTACT PLATING</b>	Gold
<b>CONTACT TYPE</b>	PCB
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Neoprene
<b>LAYOUT</b>	15
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	14
<b>MATING CYCLES</b>	250
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C



<b>RECEPTACLE TYPE</b>	Jam Nut Receptacle
<b>NUMBER OF CONTACTS</b>	15
<b>NUMBER OF CAVITY #16</b>	1
<b>NUMBER OF CAVITY #20</b>	14
<b>NUT MATERIAL</b>	Aluminium
<b>SALT SPRAY</b>	500 hour

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

:

---



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

