

# Eaton UTS714D19SW

Plastic jam nut receptacle, without backshell, with 19 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS714D19SW

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS714D19SW
<b>PRODUCT LENGTH/DEPTH</b>	25.3 mm
<b>PRODUCT HEIGHT</b>	34.9 mm
<b>PRODUCT WIDTH</b>	34.9 mm
<b>PRODUCT WEIGHT</b>	24.3 g
<b>COMPLIANCES</b>	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	5 A UL 5 A IEC
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against acid bath  Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	4 A CSA 5 A IEC 5 A UL
TEST VOLTAGE	250 V UL 32 V IEC 250 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	19
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

