



Eaton UTS714D5PZ32

Plastic jam nut receptacle & hold down clips, without backshell, with 5 male PCB contacts, IP68/69K in unmated conditions, keying Z; UTS714D5PZ32

□□□□

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714D5PZ32
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	20.7 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details)

□□□□

□□

CURRENT RATING	16 A IEC
	12 A UL
ENVIRONMENTAL CONDITIONS	RoHS
	REACH
ENVIRONMENTAL RESISTANCE	Flammability rating UL94 HB
	Resistant against mineral oil
ENVIRONMENTAL RESISTANCE	Resistant against acid bath
	UV resistant, no degradation after 5 years of exposure in natural environment
ENVIRONMENTAL RESISTANCE	Resistant against basic bath
	Resistant against oil
ENVIRONMENTAL RESISTANCE	Resistant against gasoline
	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	16 A IEC
	12 A CSA
TEST CURRENT	12 A UL
	600 V UL
TEST VOLTAGE	150 V IEC
	600 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	5
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	5

NUMBER OF CAVITY #16	5
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

